



## 'ENTAL' ENLARGING LENSES



The specially designed range of 'Ental' lenses has met with an enthusiastic welcome from discerning and critical users, as enlargements made with these lenses retain all the detail, brilliance and gradations of the negative. They are supplied in satinchrome mountings, fitted

461

with positive click-stop iris diaphragms which are scaled in exposure stop markings. The iris operating ring is extended prominently to facilitate dark room operation.

Lens	Aperture	Plate covered at full aperture.		Focus rom Flange Screw	R.P.S. Flange Screw thread
		in.	mm.	at infinity.	
50 mm.	f/3·5	$1 \times 1\frac{1}{2}$	24×36	1·8-in.	1 <del>1</del> -in.
80 mm.	f/4·5	$2\frac{1}{4} \times 2\frac{1}{4}$	60 × 60	2·8-in.	1 <b>‡-in.</b>
108 mm.	f/4·5	$2\frac{1}{2} \times 3\frac{1}{2}$	65×90	3·8-in.	1 <u>1</u> -in.
5-in.	f/4·5	31×41	80×110	4.6-in.	1½-in.

TAYLOR, TAYLOR & HOBSON LTD. 150 HOLBORN, LONDON, E.C.1